


# Kinghelm®

REVISIONS				
REV NUMBER	DESCRIPTION	DWN	CHK	DATE
A	DESIGN			

100±10mm



- NOTES:
- ELECTRICAL:
    - VOLTAGE RATING: 60V AC RMS.
    - FREQUENCY RANGE: DC-3GHz
    - VSWR: 1.3 MAX.
    - CHARACTERISTIC IMPEDANCE: 50 OHMS
  - MATERIAL SEE TABLE:
  - ALL COMPONENTS ARE ROHS COMPLIANT.

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
②	端子	高仿 1.37 一代端子, 镀金	2
①	线材	1.37黑色同轴线, OD:1.37	AS

深圳市金航标电子有限公司  
www.kinghelm.com.cn  
型号: KHA(RG1.37)-TX100B-IPEX 0755-83044319

ALL DIMENSION ARE IN MM		DRAWN		DATE		TITLE	
ENG.	Ellis	2018 /06/22	2018 /06/22	一代端子, 同向, 线长100MM			
MFG.	Alcon	2018 /06/22					
Q.A.	Jeff	2018 /06/22					

COMPUTER GENERATED  
DO NOT SCALE  
THIS DRAWING

PROJECTION

GENERAL TOLERANCE FOR  
ANGLES X.X X.XX X.XXX  
±1° ±0.3 ±0.25 ±0.150

SIZE Number

SCALE: Free

TYPE

SHEET OF 1

REV A

CUSTOMER P/N:

4 3 2 1