








	REV	SI	ON	DESCR	PTI	ON	CHECK	APP	DATE	REV.	NOTI	CE	NO
	1												
	2												
	3												



PCB PATTERN (TOP VIEW)




SEC.A-A




PERFORMANCE

- 1、Insulation Resistance: 1000m Ω Min.At DC 500V
- 2、Dielectric Withstanding Voltage For 1 Minute At AC 700V
- 3、Contact Resistance 30m Ω MAX. at 10mA and 20mV MAX.(Initial)
- 4、Current Rating: 1A max.
- 5、Operation Temperature -55℃ ~+175℃
- 6、Life Span 15,000 Times (Mechanical)
- 7、Operation Force 1.0 Kg MAX

APPL ICABLE IC



6	SOP-28-U01-003	ADAPTER	PEI/PES	1	BLACK	TOLERANCE	PROJECTION		GENERAL TOLERANCES	±0.10	TITLE	SOP28-1.27 SOCKET
5	SOP-28-U01-002	COVER	PEI/PES	1	BLACK				REV	A	CLASS	SOP24(28)-1.27-TP08NT
4	30-B-4515X	SPRING	SUS	4	FOR COVER	X ± 0.50	DIMENSION:	mm	SCALE:	1:1	DRW. NO	OTS-24(28)-1.27-04
3	SOP-28-U01-001	BASE	PEI/PES	1	BLACK	X X ± 0.25	APP:		DATE:			
2	SOP-28-MSBR-02	CONTACT	BeCu	12	Au PLATING	X XX ± 0.10	CHECK:		DATE:			
1	SOP-28-MSBR-01	CONTACT	BeCu	12	Au PLATING	X XXX ± 0.05	DEGK:	ENG03	DATE:			
No	Part Number	Name	Material	Q/ty	Note							