









PCB PATTERN (TOP VIEW)





Insertion



PERFORMANCE

- 1、Insulation Resistance: 1000mΩ Min.At DC 500V
- 2、Dielectric Withstanding Voltage For 1 Minute At AC 700V
- 3、Contact Resistance 30mΩ MAX. at 10mA and 20mV MAX.(Initial)
- 4、Current Rating: 1A max.
- 5、Operation Temperature -55°C ~+125°C
- 6、Life Span 15,000 Times (Mechanical)
- 7、Operation Force 1.0 Kg MAX

APPL ICABLE IC



5	SOP-16-U01-002	COVER	PEI/PES	1	BLACK	TOLERANCE	PROJECTION	GENERAL TOLERANCES	±0.10	TITLE	SOP16-1.27 SOCKET
4	30-B-4515X	SPRING	SUS	4	FOR COVER	X. ± 0.50	DIMENSION: mm	R E V	A	CLASS	SOP14(16)-1.27-TP04NT
3	SOP-16-U01-001	BASE	PEI/PES	1	BLACK	X. X ± 0.25	APP:	SCALE: 1:1	DATE:	DRW. NO	SOP-14/16-1.27-S01
2	SOP-16-MSBR-02	CONTACT	BeCu	7	Au PLATING	X. XX ± 0.10	CHECK:	DATE:			
1	SOP-16-MSBR-01	CONTACT	BeCu	7	Au PLATING	X. XXX ± 0.05	DEGK: ENG02	DATE: 20170318			
No	Part Number	Name	Material	Q/ty	Note						

