







	REVISION	DESCRIPTION	CHECK	APP	DATE	REV.NOTICE.NO
△ 1						
△ 2						
△ 3						



PCB PATTERN (TOP VIEW)





Insertion



PERFORMANCE

- Insulation Resistance: 1000mΩ Min.At DC 500V
- Dielectric Withstanding Voltage For 1 Minute At AC 700V
- Contact Resistance 30mΩ MAX.at 10mA and 20mV MAX.(Initial)
- Current Rating: 1A max.
- Operation Temperature -55℃ ~+175℃
- Life Span 15,000 Times (Mechanical)
- Operation Force 1.0 Kg MAX

APPL ICABLE IC



5	SOP-16-U01-002	COVER	PEI/PES	1	BLACK	TOLERANCE	PROJECTION		GENERAL TOLERANCES		±0.10	TITLE	SOP16-1.27 SOCKET	
4	30-B-4515X	SPRING	SUS	4	FOR COVER				R E V	A	CLASS	SOP16-1.27-TP01NT		
3	SOP-16-U01-001	BASE	PEI/PES	1	BLACK				X. ±0.50	DIMENSION: mm		SCALE: 1:1	DRW.NO	SOP-8/16-1.27-S01
2	SOP-16-MSBR-02	CONTACT	BeCu	8	Au PLATING				X.X ±0.25	APP:		DATE:		
1	SOP-16-MSBR-01	CONTACT	BeCu	8	Au PLATING				X.XX ±0.10	CHECK:		DATE:		
No	Part Number	Name	Material	Q/ty	Note	X.XXX ±0.05	DEGK: ENG02		DATE: 20150606					