





	REVISION	DESCRIPTION	CHECK	APP	DATE	REV.NOTICE.NO
△ 1						
△ 2						
△ 3						






PCB PATTERN (TOP VIEW)




PERFORMANCE

- 1、Insulation Resistance: 1000m Ω Min.At DC 500V
- 2、Dielectric Withstanding Voltage For 1 Minute At AC 700V
- 3、Contact Resistance 30m Ω MAX.at 10mA and 20mV MAX.(Initial)
- 4、Current Rating: 1A max.
- 5、Operation Temperature -55℃ ~+175℃
- 6、Life Span 15,000 Times (Mechanical)
- 7、Operation Force 1.0 Kg MAX

APPL ICABLE IC



SEC.A-A



6	SOP-28-U01-003	ADAPTER	PEI/PES	1	BLACK	TOLERANCE	PROJECTION		GENERAL TOLERANCES	±0.10	TITLE	SOP28-0.65 SOCKET
5	SOP-28-U01-002	COVER	PEI/PES	1	BLACK	X. X ± 0. 50	DIMENSION:	mm	R E V	A	CLASS	SOP16(28)-0.65-TP02NT
4	30-B-4515X	SPRING	SUS	4	FOR COVER	X. XX ± 0. 25	APP:		SCALE:	1:1	DRW.NO	SOP-8/14/16/20/24/28-0.65-M02
3	SOP-28-U01-001	BASE	PEI/PES	1	BLACK	X. XX ± 0. 10	CHECK:		DATE:			
2	SOP-28-MSBR-02	CONTACT	BeCu	8	Au PLATING	X. XXX ± 0. 05	DEGK:	ENG02	DATE:	20150727		
1	SOP-28-MSBR-01	CONTACT	BeCu	8	Au PLATING							
No	Part Number	Name	Material	Q/ty	Note							