	REVISION DESCRIPTION	CHECK	APP	DATE	REV. NOTICE NO
△1					
△2					
△3					



APPLICABLE IC



PCB PATTERN (TOP VIEW)









CONTAC TIP DETAIL

PERFORMANCE

1、Insulation Resistance: 1000MΩ Min.At DC 500V
2、Dielectric Withstanding Voltage For 1 Minute At AC500V
3、Contact Resistance(Initial) 30mΩ MAX at 10mA
4、Rated Current: 1.0A.
5、Operation Temperature range -65°C ~+150°C
6、Insertion Min10000 cycle (Mechanical)
7、Material: Body:PAI,PES; Contact:BeCu,Au plating(Ni-base)

No	Part Number	Name	Material	Q/ty	Note
10	30-B-4515X	SPRING	SUS	1	FOR COVER
9	QFP64-0.5-FFC	FLOATING CARRIER	PEI/PES	1	BLACK
8	QFP64-0.5-FSB	SWINGING BLOCK	PEI/PES	1	BLACK
7	QFP64-0.5-FCR	COVER	PEI/PES	1	BLACK
6	QFP64-0.5-FLH	LATCH	PEI/PES	1	BLACK
5	QFP64-0.5-FBY	BODY	PEI/PES	1	BLACK
4	QFP64-0.5-FCE	CORE	PEI/PES	1	BLACK
3	QFP64-0.5-FCTC	CONTACT	BeCu	24	FOR COVER
2	QFP64-0.5-FCTB	CONTACT	BeCu	20	BLACK
1	QFP64-0.5-FCTA	CONTACT	BeCu	20	Au PLATING

PROJECTION		GENERAL TOLERANCES	±0.10	TITLE	QFP64-0.5 SOCKET
		REV	A	CLASS	QFP64-0.5-CP01N
DIMENSION: mm		SCALE: 1:1		DRW. NO	03
APP:		DATE:			
CHECK:		DATE:			
DEGK: ENG03		DATE: 20141013			

HMILU