






Recommended P.C.B Layout



TYPE 1 (无引脚)



TYPE 2 (打引脚)

SECTION A-A

技术指标 (Technical Index):

- 1. 温度范围 (Temperature range): -25° C~+85° C.
- 2. 额定电压 (Rated voltage): 600V, AC, DC.
- 3. 额定电流 (Rated current): 5.0A AC, DC.
- 4. 接触电阻 (Contact resistance): ≤20mΩ.
- 5. 耐压值 (Withstanding voltage): 1500V AC/minute.
- 6. 绝缘电阻 (Insulation resistance): ≥1000MΩ.

CKT	A	B
02		6.00
04	3.00	9.00
06	6.00	12.00
08	9.00	15.00
10	12.00	18.00
12	15.00	21.00
14	18.00	24.00
16	21.00	27.00
18	24.00	30.00
20	27.00	33.00
22	30.00	36.00
24	33.00	39.00

APPROVALS				DATE			
DRAWN		G.M.Chen		2014/11/26		EALON 德之源®	
CHECKED						ELECTRONICS CO.,LTD	
APPROVALS						TITLE: 3.00mm Crimp Style Connectors	
TOLERANCES ARE		30~0.15 ±0.30		10~0.10 ±0.20		PART NO. X3020WV-XXA	
		5~0 ±0.10		±2°		UNIT: mm	
						SCALE: 1:1	
						DRAWING NO.	
						SHEET 1 OF 1	
						PROJ. 1	