





注：本板为禁止转输、复制、编辑、修改、以及用其内容进行交流



REV	EC.N NO.	CONTENT	CHK	DATE
-----	----------	---------	-----	------

NOTES1:

UL Standard

1.

Use group	B	C	D
Rated Current	15A	—	10A
Rated Voltage	300V	—	300V

3.Torque value: M2.5, 3.54Lb.in

4.Wire range: 28~12AWG

IEC Standard

1. Pollution Degree	3	2	2
Overvoltage Category	III	III	II
Rate Impulse Voltage(KV)	/	/	/
Rate Voltage(V)	/	320V	/
Rate Current(A)	/	12A	/

2. Torque value: M2.5, 0.4Nm

3.wire range: 1.0~2.5mm²

NOTES2:

- 1.Housing: PA66 (UL94V-0)
- 2.Cover: PA66 (UL94V-0)
- 3.Cage: Brass (Ni Plated)
- 4.Clamp: Copper alloy (Ni Plated)
- 5.Screw: Steel (M2.5,Zn Plated)

NOTES3:

- 1.Pitch: 5.08mm Poles: 02-24P
- 2.Stripping length: 7-8mm
- 3.Operating temperature: -40℃~+105℃
- 4.RoHS Compliance

How to order

MXZEDGKB - 508 - XXP - XXXX - XX - X - X

产品型号 间距 颜色 极数 A-Z其他定制
0-Y一字螺丝
1-S十字螺丝
2-P平头十字螺丝

灰色:GY 橙色:OE 01:常規顏色
蓝色:BU 红色:RD 02-99:
黑色:BK 透銅色:TT 定制顏色
綠色:GN 黃色:YW
透銅色:TT 白色:WE

Cu:銅方塊
Fe:鐵方塊

Pitch Range In mm		Nominal Dimension Range In mm						—	□
Over 6	Over 10	Over 10	Over 30	Over 60	Over 100	Over 100	Over 150	0.1/10	
TO 6	TO 10	TO 24	TO 30	TO 60	TO 100	TO 150		≤	
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30	±2°	

ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTE
DWG.	CHK	DATE	22.09.14	UNITS	MM
CHK		DATE		SCALE	1:1
APP.		DATE		NAME	MXZEDGKB-5.08-XXP
CIXI MAIXU ELECTRONICS CO.,LTD					DWGNO.
慈溪市迈旭电子有限公司					