

NOTES:

MATERIAL:

- 1.HOUSING MATERIAL :GLASS FILLED POLYESTER(UL94V-0).
- 2.CONTACT MATERIAL :PHOSPHOR BRONZE $\phi 0.46\text{mm}$ (C5100).
- 3.PLATING :GOLD PLATING OVER NICKEL.
- 4.SHIELD: COPPER ALLOY 0.20mm THICKNESS PLATING NI.

ELECTRICAL:

- 1.VOLTAGE RATING :125 VAC RMS.
- 2.CURRENT RATING :1.5 AMP.
- 3.CONTACT RESISTANCE :50 MILLIOHMS MAX.
- 4.INSULATION RESISTANCE :500 MEGOHMS MIN @ 500V DC.
- 5.DIELECTRIC WITHSTANDING RESISTANCE :1000V AC RMS 50Hz. 1MIN.

MECHANICAL:


- 1.DURRABILITY :750 CYCLES MIN.
- 2.PCB RETENTION PRE-SOLDER :1 LB MIN.

ENVIRONMENTAL:

- 1.STORAGE : -40°C TO $+85^{\circ}\text{C}$.
2. OPERATION : 0°C TO 70°C .

MATES WITH MODULAR PLUG CONFORMING TO FCC PART 68,SUBPART F.

PART NUMBER:



REVISION RECORD				
REV	ECO	DESCRIPTION	DRFT	CHKD
△		原始版本		

DETACHED LISTS		设计 zhangwei	日期 13.03.10	深圳市连欣科技有限公司	
一般公差		审核	日期		
MM	±	批准 zhang ke	日期 13.03.10	系列	名称
.0 ± 0.20	±	材料:			RJ45 1*2双层 (正弹)
.00 ± 0.15	±	数量:		图号 △ JR-99B-2X1-001	版本
.000 ± 0.075	±	表面处理:		料号: XDRJ-1609-001	A4 A
角度 ± 0.01°		比例: 1:1		不按比例	共 X 页 第 Y 页
第三角视图					