



REV	DESCRIPTION	DATE



Recommended PCB Board Layout

SPECIFICATIONS

Current Rating: 2 Amps
 Withstanding Voltage: AC 500V
 Insulation Resistance: $1000M\Omega$ Min
 Contact Resistance: $20m\Omega$ Max
 Insulator Material: Polyester(UL94V-0) See Part Number
 Contact Material: Brass or Phosphor bronze
 Contact Plating: Au or Sn over 50μ " Ni
 Operation Temperature: -40°C to $+105^{\circ}\text{C}$

TOLERANCE		MATERIAL	UNITS mm	SCALE 1 / 1	DATE 20120718	L&X 深圳市连欣科技有限公司	TITLE 2.54 mm Female Header Single Row H=9.50mm	DWG NO. MH0254-006
.X	±0.25	X*	± 2°					
.XX	±0.15	X*X'	± 1°	APPROVAL	CHECKED zhangbin	DRAWN zhangbin	PROJ. 	PART NO. XDMH-02542-95**P
.XXX	±0.10							