







CAD FILE:



P.C.B.Land Pattern



Circuit Diagram



SPECIFICATION

Temperature	-30~+70
Rated Load	DC 30V 50mA
Contact Resistance	0.03
Insulation Resistance	100M
Withstand Voltage	AC 500V(50Hz)/min
Actuating Force	3~20N
Life	5000

Memo:

TOLERANCE
UNLESS SPECIFIED

WITHIN:
OVER :

ISSUE DATE

TITLE DC-002 DC-002A 电源座

UNIT:mm

PART NO: XDJK-002A-P11/P13

SCALE:5:1

L&X 深圳市连欣科技有限公司