

REVISION RECORD				
REV	ECO	DESCRIPTION	DRAFT	CHKD

NOTES:

MATERIAL:

- 1.HOUSING MATERIAL :GLASS FILLED POLYESTER(UL94V-0).
- 2.CONTACT MATERIAL :PHOSPHOR BRONZE $\phi 0.46\text{mm}$ (C5100).
- 3.PLATING :GOLD PLATING OVER NICKEL.
- 4.SHIELD: COPPER ALLOY(OR STEEL ALLOY) 0.20mm THICKNESS PLATING NI.
- 5.LED: OPTION.

ELECTRICAL:

- 1.VOLTAGE RATING :125 VAC RMS.
- 2.CURRENT RATING :1.5 AMP.
- 3.CONTACT RESISTANCE :50 MILLIOHMS MAX.
- 4.INSULATION RESISTANCE :500 MEGOHMS MIN @ 500V DC.
- 5.DIELECTRIC WITHSTANDING RESISTANCE :1000V AC RMS 50Hz. 1MIN.
- 6.LED RATINGS:FORWARD VOLTAGE:2.2 VOLTS TYPICAL.
REVERSE VOLTAGE:5 VOLTS MAXIMUM.





MECHANICAL:


- 1.DURRABILITY:750 CYCLES MIN.
- 2.PCB RETENTION PRE-SOLDER :1 LB MIN.

ENVIRONMENTAL:

- 1.STORAGE : -40°C TO $+85^{\circ}\text{C}$.
2. OPERATION 0°C TO 70°C .

MATES WITH MODULAR PLUG CONFORMING TO
FCC PART 68,SUBPART F.



DETACHED LISTS	 MM (INCH)		设计 ZHANG WEI	日期 14.03.10	 深圳市连欣科技有限公司 名称 RJ45 180度立式插板+LED灯 DIP 图号: JR-52-008 料号: XDRJ-5224-0081 不按比例
	一 般 公 差 性		审核	日期	
	MM .0 ± 0.20 .00 ± 0.15 .000 ± 0.075		批准 ZHANG KE	日期 14.03.10	
			材料: 材料		
	角度 ± 0.01°		数量: 数量		
			表面处理: 表面处理		
	第三角视图		比例: 比例		