




MECHANICAL:



P.C.B RECOMMENDED HOLE LAYOUT SEEN FROM COMPONENT SIDE.
ALL CENTERLINE DIMENSIONS ARE BASIC

ELECTRICAL SPECIFICATIONS@25°C UNLESS OTHERWISE NOTED:

NOTES:

ELECTRICAL:

- 1. VOLTAGE RATING : 125 VAC RMS.
- 2. CURRENT RATING : 1.5 AMP.
- 3. CONTACT RESISTANCE : 30 MILLIOHMS MAX.
- 4. INSULATION RESISTANCE : 500 MEGOHMS MIN @ 500 VDC.
- 5. DIELECTRIC STRENGTH : 1000 VAC RMS 50Hz or 60Hz, 1MIN.

MECHANICAL:

- 1. HOUSING & INSERT MATERIAL : PBT UL94V-0.
- 2. CONTACT MATERIAL : DIAMETER 0.45MM PHOSPHOR BRONZE
GOLD PLATING OVER NICKEL.
- 3. SHIELD : 0.20 ~ 0.25MM THICKNESS BRASS WITH NICKEL PLATED
- 4. MATING/UNMATING FORCE : 2.2KG.F MAX.
- 5. RETENTION STRENGTH : 7.7KG.F MIN BETWEEN JACK AND PLUG.
- 6. OPERATING LIFE : 600 CYCLES MIN.

ENVIRONMENTAL:

- 1. STORAGE : -10°C ~ +40°C RELATIVE HUMIDITY<70%.
- 2. OPERATION : -40°C ~ +70°C.

Remark:

- 1. Tolerances Unless Otherwise Specified
.0±0.25 .00±0.20 .000±0.10
- 2. The mark with ★ is the key inspection dimension for QC

核准:	WANGLIHUA	審核:	TTAO	製圖:	JACK JIN	L&X 深圳市连欣科技有限公司		
更改:	變更內容:	日期:	修改:	核准:				
A		12-Dec-2013	JACK JIN	TTAO		尺寸單位: mm	.X± 0.25	RJ45-CONNECTOR 1X1 TAB-DOWN W/ LED W/O SHIELD
						比例: 1:1	.XX± 0.13	NO: XDRJ-5805-035 REV: A