

REVISION RECORD				
REV	ECD	DESCRIPTION	DFT	CHKD

NOTES:

MATERIAL:

- 1.HOUSING MATERIAL :GLASS FILLED POLYESTER(UL94V-0).
- 2.CONTACT MATERIAL :PHOSPHOR BRONZE $\phi 0.46\text{mm}$ (C5100).
- 3.PLATING :GOLD PLATING OVER NICKEL.
- 4.SHIELD,COPPER ALLOY(OR STEEL ALLOY) 0.20mm THICKNESS PLATING NI.
- 5.LED: OPTION.

ELECTRICAL:





- 1.VOLTAGE RATING :125 VAC RMS.
- 2.CURRENT RATING :1.5 AMP.
- 3.CONTACT RESISTANCE :50 MILLIOHMS MAX.
- 4.INSULATION RESISTANCE :500 MEGOHMS MIN @ 500V DC.
- 5.DIELECTRIC WITHSTANDING RESISTANCE :1000V AC RMS 50Hz. 1MIN.
- 6.LED RATINGS:FORWARD VOLTAGE:2.2 VOLTS TYPICAL.
REVERSE VOLTAGE:5 VOLTS MAXIMUM.



MECHANICAL:

- 1.DURRABILITY:750 CYCLES MIN.
- 2.PCB RETENTION PRE-SOLDER :1 LB MIN.

ENVIRONMENTAL:

- 1.STORAGE : -40°C TO $+85^{\circ}\text{C}$.
 2. OPERATION 0°C TO 70°C .
- MATES WITH MODULAR PLUG CONFORMING TO
FCC PART 68,SUBPART F.



DETACHED LISTS			设计 ZHANG WEI 日期 13.04.10		深圳市连欣科技有限公司		
	一般公差		审核 日期				
	MM D ± 0.20 .00 ± 0.15 ODD ± 0.075		批准 ZHANG KE 日期 13.04.10		名称	RJ45插座 1*4 LED灯+弹片 (左黄右绿)	
			材料: 材料				
	角度 ± 0.01°		数量: 数量				
			表面处理: 表面处理		料号: XDRJ-5604L-0157		A3 版本
	第三角视图		比例: 比例		不按比例		
					共 X 页 第 Y 页		