


Kinghelm®

REVISIONS					
REV	NUMBER	DESCRIPTION	DWN	CHK	DATE
A		DESIGN			



NOTES:

1. ELECTRICAL:
 - 1.1. VOLTAGE RATING:DC 300V 10MS
 - 1.2. CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
 - 1.3. INSULATION RESISTANCE: 5.0M OHM/MIN.
 - 1.4. THE CABLE SHOULD BE 100% ELECTRICAL TEST
 - 1.5. IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES.
2. MATERIAL:
 - 2.1. SEE TABLE
3. ALL COMPONENTS ARE RoHS COMPLIANT.

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
③	套管	OD:2.5* 15 mm 套管	1
②	接头	SMA 公头直头,公针,镀金	1
①	同轴线	RG1.13黑色同轴线, OD:1.13mm	AS

深圳市金航标电子有限公司
SHENZHEN KINGHELM ELECTRON CO., LTD.

ALL DIMENSION ARE IN MM	DRI	DATE	KH-SMAJ-221-RG1.13-B120
	DRAIN. Jamy	2023/8/11	
COMPUTER GENERATED IN SOLIDWORKS	CHK. Alan	2023/8/11	
DO NOT SCALE THIS DRAWING	APP. Ellis	2023/8/11	www.kinghelm.com.cn 0755-28190160
PROJECTION	GENERAL TOLERANCE FOR ANGLES X.X X.XX X.XXX ± 1° ± 0.3 ± 0.25 ± 0.150		
SCALE: Free		TYPE	SHEET 1 OF 1

4

3

2

1

D

D

C

C

B

B

A

A