



RECOMMEND PCB LAYOUT
PCB TOLERANCE:±0.05

SPECIFICATION:
MATERIAL:
 HOUSING:LCP LG431-9731L 30% G/F UL 94V-0
 COLOR:BLACK
 CONTACT:BRASS C2680R EH.T=0.25mm
 PEG: BRASS C2680R H.T=0.30mm
FINISH:
 CONTACT: 1u" GOLD/TIN PLATING ON CONTACT AREA
 100u" MIN. TIN-LEAD PLATING ON SOLDERTAILS
 50u" MIN. NICKEL UNDERPLATING OVERALL
 PEG:100u" MIN. TIN-LEAD PLATING ON SOLDERTAILS
 50u" MIN. NICKEL UNDERPLATING OVERALL

REV.	DESCRIPTION	DATE
A/0	客户PB-070883精英特展款芯(鱼叉) 直接提交更改为精英型	20130330

深圳市连欣科技有限公司

X. #015 XX #010 XXX #005 XXXX #000 X* #5* X* #1*	DRAWN BY: 博 敏	DATE: 20130623	PART NAME: SATA7Pin SMT 全铝串口连接器
UNIT: mm [Inch]	CHECKED BY: 叶建林	DATE: 20130625	PART NO. XUTS-0762-0263
SCALE: 1:1	APPROVAL BY: Welsentdo	DATE: 20130629	MOLD NO.
SIZE: A4			PRODUCT SPEC.
			DRAW NO.