





NOTES:

1. 材质: PBT+30%GF

端子: C2680R-EH, T=0.20±0.01

SHELL: C2680-1/2H, T=0.30±0.01.

Specification

1.ELECTRICAL CHARACTERISTIC:

CONTACT RESISTANCE: 30mΩ Max

DIELECTRIC WITHSTANDING VOLTAGE: 500V AC for 1MIN

INSULATION RESISTANCE: 1000M Ω Min

2. MECHANICAL CHARACTERISTIC:

INSERTION FORCE: 35N(3.57kgf) MAX

EXTRACTION FORCE: 10~35N(1.02~3.57kgf)

DURABILITY: 1500 CYCLES

3. ENVIRONMENTAL:


OPERATING TEMPERATURE: -55°C~+85°C

4.△为品管必须管控尺寸。

5. 为巡检尺寸。

6. 整套成品配合需顺畅.

7.所有的功能测试要满足USB协会 2.0版本.



PCB Layout

[illegible]