



# Technical Data

Material  
 Contact Material: Brass/Phosphor Bronze  
 Contact plating: Nicker/Gold Flash  
 Insulator Material: Black Polyester UL94V-0  
 Standard: PBT+30%G F

Electrical  
 Current rating: 3.0Amps/contact max  
 Contact resistance: ≤20mΩ/ contact  
 Insulation resistance: ≥1000MQ at V=100V  
 Withstanding Voltage: 1000V AC/minute

Mechanical  
 Operaing temperature: -40 C to +105C

HY-2540-A 0 X X

HOUSING COLOR:  
 B:BLACK BL:BLUE Y:YELLOW  
 W:WHITE GR:GREEN R:RED

CONTACT PLATING:  
 GF:FULL GOLD FLASH  
 NI:NICKEL  
 GN:GOLD+NICKEL

HEIGHT:  
 0:6mm  
 1:6.5mm

HOUSING TYPE:  
 A:OPEN B:CLOSE C:LONG

		new		2015/5/3	A	瀚源	
ECN BO.		DESCRIPTION.		DATE.	REV.		
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER	SCALT: 1/2		SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	HY-2540-A0XX	UNLESS OTHERWISE SPECIFIED,TOLERANCE:	X.	±0.25
			MODEL NAME	HY-2540-A0XX		X.x	±0.20
			3RD ANGLE PROJ	HanElectricity Co.,LTD		X.xx	±0.15
				FILE.NO.			