


Kinghelm®

REVISIONS					
REV	NUMBER	DESCRIPTION	DWN	CHK	DATE
A		DESIGN			



- NOTES:
- ELECTRICAL:
 - VOLTAGE RATING:DC 300V 10MS
 - CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
 - INSULATION RESISTANCE: 5.0M OHM/MIN.
 - THE CABLE SHOULD BE 100% ELECTRICAL TEST
 - IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES.
 - MATERIAL:
 - SEE TABLE
 - ALL COMPONENTS ARE RoHS COMPLIANT.

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
③	套管	OD:2.5* 15 mm 套管	1
②	接头	SMA 公头直头,公针,镀金	1
①	同轴线	RG1.78棕色同轴线, OD:1.78mm	AS
深圳市金航标电子有限公司 SHENZHEN KINGHELM ELECTRON CO.,LTD.			
ALL DIMENSION ARE IN MM		DRI	DATE
		DRAIN. Jamy	2023/8/11
COMPUTER GENERATED IN SOLIDWORKS		CHK. Alan	2023/8/11
DO NOT SCALE THIS DRAWING		APP. Ellis	2023/8/11
PROJECTION		GENERAL TOLERANCE FOR ANGLES XX X.XX X.XXX ± 1° ± 0.3 ± 0.25 ± 0.150	
		KH-SMAJ-221-RG1.78-70	
		www.kinghelm.com.cn 0755-28190160	
		SCALE: Free	SHEET 1 OF 1