







目录 INDEX	设计内容 MODIFICATION	日期 DATE	修改人 DRAW	核准 APPROVE



RECOMMEND PCB LAYOUT



电气特性:Electrical:
 1. 额定电流: Current Rating: 1.5A/contact terminal
 2. 额定电压: Voltage Rating: 30V DC
 3. 接触阻抗: Contact Resistance: 30 milliohms MAX
 4. 耐电压: Dielectric Withstanding Voltage: 500 V AC AT Sea Level
 5. 绝缘阻抗: Insulation Resistance: 1000MEGA ohms MIN
 物理性能: Mechanical:
 1. 插拔力: Connector Mate and Unmate Force: Mate force: 3.75kgf (MAX)
 Umate force: 1.02kgf (MIN)
 2. 端子保持力: Terminal Retention: 1.2kgf (MIN)
 原材料: Material:
 1. 塑胶: Housing: High Temperature Thermoplastics, UL 94V-0 PBT White/Black
 2. 端子: Contact: Copper Alloy C2680
 3. 外壳: Shell: SPCC
 电镀: Finish:
 1. 端子: Contact: Plated Gold in Mating Area: Tin On Solder Tails
 2. 外壳: Shell: Nickel Plating

产品图
MANUFACTURE DWG

公差一览表
TOLERANCE UNLESS OTHERWISE

单位 UNITS	MM		INCH
.X	±0.20	.X	±---
.XX	±0.10	.XX	±---
.XXX	±0.05	.XXX	±---

2011. 03. 14

L&X 深圳市连欣科技有限公司

产品名称 USB A/F 侧插短体卷边

料号 XBDF-0524-08

制图 何杰

设计 何杰

审核 何杰

核准 何杰