



PCB LAYOUT

SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
- 4、Contact Resistance: $20\text{m}\Omega$ Max
- 5、Insulation Resistance: $1000\text{M}\Omega$ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material: Wafer LCP, UL94V-0
PIN Brass Tin-plated
Solder tad Brass Tin-plated

编号	尺寸 (mm)		
	A	B	C
A2504-02AWB	2.50	7.50	10.00
A2504-03AWB	5.00	10.00	12.50
A2504-04AWB	7.50	12.50	15.00
A2504-05AWB	10.00	15.00	17.50
A2504-06AWB	12.50	17.50	20.00
A2504-07AWB	15.00	20.00	22.50
A2504-08AWB	17.50	22.50	25.00
A2504-09AWB	20.00	25.00	27.50
A2504-10AWB	22.50	27.50	30.00
A2504-11AWB	25.00	30.00	32.50
A2504-12AWB	27.50	32.50	35.00

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	钱岳生		料号 PART NO.	A2504-nAWB		版本 REV.	A
			$X \pm 0.25$	$X \pm 2'$		2013、07、01		品名	HA卧贴		页次	1/1
			$.X \pm 0.20$	$.X \pm 1'$	审核	2013、07、03	张名	TITLE	WAFER SMT TYPE		SHEET	
			$.XX \pm 0.15$	$.XX \pm 0.5'$	核准	2013、07、05	张名	客户料号 CUTM. NO.	深圳市金航标电子有限公司		www.kinghelm.com.cn	
			$.XXX \pm 0.10$	$.XXX \pm 0.5'$	单位 UNITS	MM	比例 SCALE	1:1	KH-A2504-02AWB		0755-28190160	