


**Kinghelm®**

REVISIONS					
REV	NUMBER	DESCRIPTION	DWN	CHK	DATE
A		DESIGN			



**NOTES:**

1. ELECTRICAL:
  - 1.1. VOLTAGE RATING:DC 300V 10MS
  - 1.2. CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
  - 1.3. INSULATION RESISTANCE: 5.0M OHM/MIN.
  - 1.4. THE CABLE SHOULD BE 100% ELECTRICAL TEST
  - 1.5. IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES.
2. MATERIAL:
  - 2.1. SEE TABLE
3. ALL COMPONENTS ARE RoHS COMPLIANT.

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
④	接头	国产IPEX四代1.37端子	
③	套管	OD:2.5* 15 mm 套管	1
②	接头	SMA 公头直头,公针,镀金	1
①	同轴线	RG1.37黑色同轴线, OD: 1.37mm	AS

**深圳市金航标电子有限公司**  
**SHENZHEN KINGHELM ELECTRON CO., LTD.**

ALL DIMENSION ARE IN MM	DRI	DATE	KH-SMAJ-IPEX4-RG1.37-B300
	DRAIN. Jamy	2023/8/11	
COMPUTER GENERATED IN SOLIDWORKS	CHK. Alan	2023/8/11	
DO NOT SCALE THIS DRAWING	APP. Ellis	2023/8/11	
PROJECTION	GENERAL TOLERANCE FOR ANGLES X.X X.XX X.XXX ± 1° ± 0.3 ± 0.25 ± 0.150		www.kinghelm.com.cn 0755-28190160
SCALE: Free		TYPE	SHEET 1 OF 1

4

3

2

1

D

D

C

C

B

B

A

A