







RoHS
Compliant




REV.	ECN. NO.	DR.	DATE
A	NEW	Jeff	081011

NOTES:
1.MATERIAL:
HOUSING:LCP 30% G/F UL94 V-0
COLOR:BLACK
CONTACT:PHOSPHOR BRONZE C5191H T=0.25mm
BOARD LOCK:BRASS C2680H T=0.25mm
2.FINISH:
CONTACT:GOLD FLASH/TIN PLATING ON CONTACT AREA
100u" MIN.TIN PLATING ON SOLDER TAILS
50u" MIN.NICKEL UNDERPLATING OVER ALL
BOARD LOCK:100u"MIN.TIN PLATING ON SOLDER TAILS
50u"MIN.TIN NICKEL UNDERPLATING OVER ALL



RECOMMEND P.C.B LAYOUT (T=1.2)

Title: SATA 15+7 连接器母座 板上 Tepy SMT H=6.74 MM				L&X 深圳市连欣科技有限公司			
tolerances		app.		units ☒ mm ☐ inch	part no: XUTS-2207-067		
linear	angles				dwg no.		
.x ±0.38	x.* ±5'	chk.		size A4	112207ATA		
.xx ±0.25	.x' ±2"						
.xxx ±0.15	.xx' ±1"	dr.	Jeff				
projection 	revision. A	date.	081011	scale 4:1		sheet 1/1	