

RoHS

REV.	ECN NO.	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2023.09.05

技术参数 (SPECIFICATIONS)

额定电流(Current rating) : 5A
额定电压(Voltage rating) : 250V AC DC
耐压值(Withstand voltage) : 1500V AC
绝缘电阻(Insulation resistance) : $\geq 1000\text{M}\Omega$
接触电阻(Contact resistance) : $\leq 20\text{m}\Omega$
工作温度(Working temperature) : $-25^{\circ}\text{C} + 85^{\circ}\text{C}$
材料 (MATERIAL)
绝缘体(Insulator Material) : LCP UL 94V-0 Black
接触材料(Contact Material): Brass Tin Plated over Nickel
焊片(Welding piece): Brass Tin-Plated
匹配型号(Matching model) : P3025-2xXX series







产品名称说明 :

M3025VS-2xXX-BK
1 2 3

1.序列号

2.Pin位数 : 2-24
04=2x02

3.颜色 : 黑色=BK



PCB LAYOUT

孔位 poles	A	B	孔位 poles	A	B
2	0	6.6	14	18.0	24.6
4	3.0	9.6	16	21.0	27.6
6	6.0	12.6	18	24.0	30.6
8	9.0	15.6	20	27.0	33.6
10	12.0	18.6	22	30.0	36.6
12	15.0	21.6	24	33.0	39.6

X.±0.50	X.°±
.X±0.25	.X°±
.XX±0.15	.XX°±
.XXX±0.10	.XXX°±
UNITS:	mm

THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF XFCN
AND SHALL NOT BE REPRODUCED,
COPIED OR CUED IN ANY MANNER
WITHOUT THE PRIOR WRITTEN CONSENT
OF XFCN

PART NO.:
M3025VS-2xXX-BK

TITLE:
3.00mm Crimp Style Connectors

APPD:

CHKD:

DRAW: Tong.Deng 2023.09.11


XFCN兴飞连接器

0769-82001899

www.xfconn.com

DWG NO:

/



SCALE	SHEET	REV.
NONE	1/1	A1