







REV.	ECN NO OR DESCRIPTION	REVISED	DATE



[Schematic]

NOTES:


- 1.MECHANICAL:**
 1>.Operation force: 1000gf Max.
 2>.Operation Temperature: -30°C to +85°C.
 3>.Storage Temperature: -40°C to +85°C.
 4>.Mechanical Life: 3000 cycles operations.
 5>.Resistance to Soldering: 260±5°C for 3-5 Seconds.
 6>.Please keep switch in "OFF" when welding.

2.MATERIAL:

- 1>.Base: UL94V-0 PBT Thermoplastic / Color:Black.
 2>.COVER: UL94V-0 PBT Thermoplastic / Color:Red, Black, Blue.
 3>.ACTUATOR: UL94V-0 PBT High Thermoplastic / Color: White.
 4>.TERMINAL: Copper alloy with gold plating for 1.5u".

3.ELECTRICAL:

- 1>.Non-switching Rating:100mA at 50VDC.
 2>.Switching Rating: 25mA at 24VDC.
 3>.Contact Resistance: Inital 50mΩ Max.
 Contact Resistance: After life 100mΩ Max.
 4>.Insulation Resistance:100MΩ Min at 500VDC.
 5>.Dielectric Strength: 500VAC for 60seconds.
 6>.Switch Capacitance: 5PF Max at 1MHZ.



PIN位	2PIN	3PIN	4PIN	5PIN	6PIN	7PIN	8PIN	9PIN	10PIN	12PIN	
DIM.A (长度)	6.64	9.18	11.72	14.26	16.80	19.34	21.88	24.42	26.96	32.04	
DIM.B (长度)	2.54	5.08	7.62	10.16	12.70	15.24	17.78	20.32	22.86	27.94	
PART NO.	凸柄 (T)	DT-02LT	DT-03LT	DT-04LT	DT-05LT	DT-06LT	DT-07LT	DT-08LT	DT-09LT	DT-10LT	DT-12LT
盖子/蓝色(L)	短柄 (D)	DT-02LD	DT-03LD	DT-04LD	DT-05LD	DT-06LD	DT-07LD	DT-08LD	DT-09LD	DT-10LD	DT-12LD
PART NO.	凸柄 (T)	DT-02HT	DT-03HT	DT-04HT	DT-05HT	DT-06HT	DT-07HT	DT-08HT	DT-09HT	DT-10HT	DT-12HT
盖子/红色(H)	短柄 (D)	DT-02HD	DT-03HD	DT-04HD	DT-05HD	DT-06HD	DT-07HD	DT-08HD	DT-09HD	DT-10HD	DT-12HD
PART NO.	凸柄 (T)	DT-02KT	DT-03KT	DT-04KT	DT-05KT	DT-06KT	DT-07KT	DT-08KT	DT-09KT	DT-10KT	DT-12KT
盖子/黑色(K)	短柄 (D)	DT-02KD	DT-03KD	DT-04KD	DT-05KD	DT-06KD	DT-07KD	DT-08KD	DT-09KD	DT-10KD	DT-12KD

UNLESS OTHERWISE SPECIFIED TOLERANCES

DECIMALS:	ANGLES:
X :±0.30	X :±2°
X.X :±0.20	X.X :±1°
X.XX :±0.10	

东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE	BY DSPV DIP SERIES PITCH 2.54mm		
DWN	xiong	PART NO. DT-XXXX	
CHKD	lee	SCALE:1:1	UNIT: mm
APVD	wang	SIZE: A4	SHEET:10F 1
REV: A4			
CUSTOMER COPY			