

NOTES:

MATERIAL:

- 1.HOUSING MATERIAL :GLASS FILLED POLYESTER(UL94V-0).
- 2.CONTACT MATERIAL :PHOSPHOR BRONZE $\phi 0.46\text{mm}$ (C5100).
- 3.PLATING :GOLD PLATING OVER NICKEL.
- 4.SHIELD COPPER ALLOY 0.20mm THICKNESS PLATING NI.

ELECTRICAL:

- 1.VOLTAGE RATING :125 VAC RMS.
- 2.CURRENT RATING :1.5 AMP.
- 3.CONTACT RESISTANCE :50 MILLIOHMS MAX.
- 4.INSULATION RESISTANCE :500 MEGOHMS MIN @ 500V DC.
- 5.DIELECTRIC WITHSTANDING RESISTANCE :1000V AC RMS 50Hz. 1MIN.

MECHANICAL:




- 1.DURRABILITY :750 CYCLES MIN.
- 2.PCB RETENTION PRE-SOLDER :1 LB MIN.


ENVIRONMENTAL:

- 1.STORAGE : -40°C TO $+85^{\circ}\text{C}$.
2. OPERATION : 0°C TO 70°C .

MATES WITH MODULAR PLUG CONFORMING TO FCC PART 68,SUBPART F.

REVISION RECORD				
REV	ECO	DESCRIPTION	DRFT	CHKD
1		原始版本		



DETACHED LISTS	 MM (INCH)		设计 zhangwei 日期 13.03.10		深圳市连欣科技有限公司				
	一般公差栏		审核 日期						
	MM .0 ± 0.20 .00 ± 0.15 .000 ± 0.075		± ± ±		批准 zhangke 日期 13.03.10		系列	名称	
					图号 03188103121		系列	RJ45 立式直插 无灯	
	角度 ± 0.01°		数量:		料号: XDRJ-5224-003			A4	A ^原
	 第三角视图		表面处理:						
			比例: 1:1		不按比例			共 X 页 第 Y 页	