






1.Specifications


Current Rating: 1Amp
Insulation Resistance: 1000MΩ Min.
Dielectric Withstanding: 300V AC/DC
Contact Resistance: 20mΩ Max.
Operating Temperature:−40°C to +105°C

2.Materials

Contact Material: Phosphor Bronze
Insulation Material: Polyester, UL 94V-0
PBT
All materials must be GP materials1U”



RECOMMENDED PCB LAYOUT
TOLERANCE:±0.05



				GENERAL TOL.		DRAW NO.	TWT-E00038	DATE	P/N. XDHF-AS0254-0852*6P	DRAW NAME: 排母PH2.54*8.5 2*6P 垫高0.4MM 双弯90度			
				X.		DESIGN:	Mike, Lee	10/16'14	SIZE: A4				
				X.X					UNIT: mm			SHEET: 1 OF 1	
AO				INITIAL RELEASE		12/26'07	Mike, Lee						
REV. ECN NO.				DESCRIPTION		DATE	DESIGN		REV. A0			SCALE: N/A	

深圳市连欣科技有限公司