






SPECIFICATIONS
Current rating :5~8.5A AC, DC
Voltage rating :250V AC, DC
Temperature range :-45°C~+105°C
Contact resistance :10mΩMax
Insulation resistance :1000MΩ Min
Withstanding voltage :1500 V AC/minute
Contact Material :Brass
Finished :Tin-plated
Housing Material :LCP UL94-V0
Color :Black

PART NO:	Dimension mm	
	A	B
C3030WT-F-2*1P		6.65
C3030WT-F-2*2P	3.00	9.65
C3030WT-F-2*3P	6.00	12.65
C3030WT-F-2*4P	9.00	15.65
C3030WT-F-2*5P	12.00	18.65
C3030WT-F-2*6P	15.00	21.65
C3030WT-F-2*7P	18.00	24.65
C3030WT-F-2*8P	21.00	27.65
C3030WT-F-2*9P	24.00	30.65
C3030WT-F-2*10P	27.00	33.65
C3030WT-F-2*11P	30.00	36.65
C3030WT-F-2*12P	33.00	39.65



P.C.B LAYOUT

TOLERANCE	
X.	--
X.X	±0.25
X.XX	±0.20
X.XXX	±0.05
ANGULAR	--

TITLE			
3.0MM Pitch Wire to Board Header			

深圳市连欣科技有限公司

DRAWN	FrOnK	VIEW	SCALE	PART NO.	REV.
CHECKED	Denise		3:1	XDWF-C3030WT-**P	A2
APPROVED	Jessico	UNIT	SIZE	DWG NO.	SHEET
		MM	A4	C3030WT-005	1 OF 1