







ÓÉ Foxit PDF Editor ±¼-
°æËÛÜÖÐ (c) by Foxit Software Company, 2004
½ÖÖÁÖÙÆ¹Àj£



RECOMMEND PCB LAYOUT
GENERAL TOLERANCE ±0.05

NOTES:
1.MATERIAL AND FINISH:
CONTACTS:COPPER ALLOR,GOLD FLASH OVER ALL;
LATCH:STAINLESS;
SHELL:STAINLESS,GOLD FLASH ON SOLDER TAILS;
HOUSING:THERMOPLASTIC,BLACK;
2.THE RETENTION FORCE OF PIN IS SET TO 200gf MIN.
3.INSERTION FORCE:2.0gf MAX,EXTRACTION FORCE;0.80gf
MIN INITIAL,0.40gf MIN AFTER 10000 CYCLES.
4.THERE SHOULD BE NO DBVIOUS BUBBLE UNDER THE
TAPE AND FLOAT AREA.

PIN NO.	SIGNAL
1	DETECT1
2	SCC1
3	DP1
4	DN1
5	PWR A
6	PWR B
7	DN2
8	DP2
9	ACC2
10	DETECT2
SHELL	GND

4	LATCH	1	SUS 304	NI PLATING
3	CONTACT	10	COPPER OLLAY	CONTACT: GOLD FLASH
2	HOUSING	1	THERMOPLASTIC	COLOR:BLACK
1	SHELL	1	SUS 304	NI 50u";MATTE TIN 50u"
NO.	DESCRIPTION	QT'Y	MATERIAL	NOTE

變更記事						PART		顏色 COLOR	BLACK		SCALE	1:1	L&X 深圳市连欣科技有限公司		
						~ 5	±0.05	材質 MATERIAL			UNIT	mm			
						5 ~ 10	±0.10								
						10 ~ 20	±0.15	設計 DESING			SIZE	A4	料號 PART NO.	XDAP-0105-0256	
						20 ~ 30	±0.20								
	A0	12. 09. 20	NEW		_____	_____	30 ~	±0.30	審核 CHECK			SHEET	1/1	品名 TITLE:	APPLE I5 CONNECT SMT
	版次 REV	日期 DATE	變 更 說 明 MODIFICATION DESCRIPTION		變更 CHANGE	核准 APPROVE	Angle	± 1°		核准 APPROVE			PROJ.		
						DIM	TOL								