


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE
PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE
WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
B	ECN 11794: Changing from "J1 MPO FEMALE..." to "J1 MPO MALE..."	4/20/2022	PHOSPODAR

WIRING MAP TYPE B		
J1	COLOR	J2
1	BLUE	12
2	ORANGE	11
3	GREEN	10
4	BROWN	9
5		8
6		7
7		6
8		5
9	YELLOW	4
10	PURPLE	3
11	ROSE	2
12	AQUA	1



LENGTH	
ITEM NO.	METERS [FEET]
MPMF8OM3BR-1	1.0 [3.28]
MPMF8OM3BR-3	3.0 [9.84]
MPMF8OM3BR-5	5.0 [16.40]
MPMF8OM3BR-10	10.0 [32.81]

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS .XX = ± .02 [.5] ± 1/32 .XXX = ± .005 [.13] ANGLES ± 1° THIRD-ANGLE PROJECTION 		APPROVALS	DATE	 an INFINITI® brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
		DRAWN BY DZINN	10/25/2021	
		CHECKED BY DFRISIELLO	10/25/2021	CATEGORY FIBER OPTICS
		APPROVED BY PHOSPODAR	10/25/2021	PRODUCT DESCRIPTION Fiber patch cable MPO Male to MPO Female, 8 fiber MMF OM3 type B, OFNR rated
		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A
		CAGE CODE 43321	ITEM NO. MPMF8OM3BR	REV. B
		SCALE: NONE	CAD FILE: MPMF8OM3BR.SLDDRW	SHEET 1 OF 1