



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	10/25/2021	PHOSPODAR

WIRING MAP TYPE A		
J1	COLOR	J2
1	BLUE	1
2	ORANGE	2
3	GREEN	3
4	BROWN	4
5		5
6		6
7		7
8		8
9	YELLOW	9
10	PURPLE	10
11	ROSE	11
12	AQUA	12



LENGTH	
ITEM NO.	METERS [FEET]
MPMM8SMAZ-1	1.0 [3.28]
MPMM8SMAZ-3	3.0 [9.84]
MPMM8SMAZ-5	5.0 [16.40]
MPMM8SMAZ-10	10.0 [32.81]

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS		DATE		 an INFINITI brand 50 High Street, West Mill, North Andover, MA 01845 USA Phone: 1.800.341.5266 1.978.682.6936	
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0		DRAWN BY DZINN		10/25/2021			
		CHECKED BY DFRISIELLO		10/25/2021			
		APPROVED BY PHOSPODAR		10/25/2021			
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] .XX = ± .02 [.5] .XXX = ± .005 [.13]		FRACTIONS ± 1/32 ANGLES ± 1°		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY FIBER OPTICS	
THIRD-ANGLE PROJECTION 		COLOR VARIATIONS MAY OCCUR		PRODUCT DESCRIPTION Fiber patch cable MPO male to MPO male, 8 fiber SMF type A, LSZH rated			
				SIZE A	CAGE CODE 43321	ITEM NO. MPMM8SMAZ	REV. A
				SCALE: NONE		CAD FILE: MPMM8SMAZ.SLDDRW	SHEET 1 OF 1