


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	08/11/2021	PHOSPODAR




ITEM NO.	LENGTH	
	METER	FEET
FCA-LASA-DPS2Z-01	1.0	3.28
FCA-LASA-DPS2Z-02	2.0	6.56
FCA-LASA-DPS2Z-03	3.0	9.84
FCA-LASA-DPS2Z-05	5.0	16.40
FCA-LASA-DPS2Z-10	10.0	32.81
FCA-LASA-DPS2Z-15	15.0	49.21

NOTES:

1. LC AND SC CONNECTOR POLISH TYPE: APC.
2. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS		DATE		<div><div><div>L-com</div><div>an INFINITI brand</div></div><div>50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936</div></div>	
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0		DRAWN BY DZINN		08/11/2021			
		CHECKED BY DFRISIELLO		08/11/2021			
		CATEGORY					
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS .XX = ± .02 [.5] ± 1/32 .XXX = ± .005 [1.3] ANGLES ± 1°		APPROVED BY PHOSPODAR		08/11/2021		FIBER OPTICS	
		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION FIBER OPTIC PATCH CABLE LC/APC TO SC/APC DUPLEX 9/125 SINGLEMODE OS2 LSZH			
THIRD-ANGLE PROJECTION 		COLOR VARIATIONS MAY OCCUR		SIZE A	CAGE CODE 43321	ITEM NO. FCA-LASA-DPS2Z	REV. A
				SCALE: NONE		CAD FILE: FCA-LASA-DPS2Z.SLDDRW	
						SHEET 1 OF 1	