



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	10/25/2021	PHOSPODAR

WIRING MAP TYPE A		
J1	COLOR	J2
1	BLUE	1
2	ORANGE	2
3	GREEN	3
4	BROWN	4
5		5
6		6
7		7
8		8
9	YELLOW	9
10	PURPLE	10
11	ROSE	11
12	AQUA	12



LENGTH	
ITEM NO.	METERS [FEET]
MPMF8SMAZ-1	1.0 [3.28]
MPMF8SMAZ-3	3.0 [9.84]
MPMF8SMAZ-5	5.0 [16.40]
MPMF8SMAZ-10	10.0 [32.81]

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13] THIRD-ANGLE PROJECTION 	APPROVALS	DATE	 an INFINITI brand	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
	DRAWN BY DZINN	10/25/2021			CATEGORY
	CHECKED BY DFRISIELLO	10/25/2021			
	APPROVED BY PHOSPODAR	10/25/2021			
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION Fiber patch cable MPO Male to MPO Female, 8 fiber SMF type A, LSZH rated			
COLOR VARIATIONS MAY OCCUR		SIZE A	CAGE CODE 43321		ITEM NO. MPMF8SMAZ
		SCALE: NONE CAD FILE: MPMF8SMAZ.SLDDRW			SHEET 1 OF 1