


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	2/4/22	JJOHNSTON



PART NUMBER	LENGTH METERS [FEET]
FCA-MMS108A00P	0.5 [1.64]
FCA-MMS108A01P	1.0 [3.28]

WIRING MAP	
MPO FIBER #	COLOR
1	N/A
2	N/A
3	BLUE
4	ORANGE
5	GREEN
6	BROWN
7	GREY
8	WHITE
9	RED
10	BLACK
11	N/A
12	N/A

NOTES:

- LC CONNECTOR ASSEMBLY POLISH TYPE: UPC
- ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5] FRACTIONS ± 1/32 .XX = ±.02 [.5] ANGLES ± 1° .XXX = ±.005 [.13] THIRD-ANGLE PROJECTION 	APPROVALS	DATE	 an INFINITI® brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY DMAY	1/24/22	
	CHECKED BY DFRISIELLO	1/28/22	
	APPROVED BY JJOHNSTON	2/4/22	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	CATEGORY FIBER OPTICS		PRODUCT DESCRIPTION PATCH CORD SM OS2 8CORES MPO(MALE, STANDARD LOSS)-LC/UPC 0.25mm PVC 8COLOUR
COLOR VARIATIONS MAY OCCUR	SIZE A	CAGE CODE 43321	
	ITEM NO. FCA-MMS108A0	REV. A	
	SCALE: NONE	CAD FILE: FCA-MMS108A0.SLDDRW	