




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	08/02/2021	PHOSPODAR



PART NUMBER	LENGTH METERS [FEET]
FOA1OOD8-001M	1.0 [3.28]
FOA1OOD8-002M	2.0 [6.56]
FOA1OOD8-005M	5.0 [16.40]
FOA1OOD8-010M	10.0 [32.80]
FOA1OOD8-012M	12.0 [39.37]

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS		DATE		<div><div>an INFINITI® brand</div></div> <div>50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936</div>		
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0		DRAWN BY MVEERAPPAN		08/01/21				
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]      FRACTIONS .XX = ± .02 [.5]      ± 1/32 .XXX = ± .005 [.13]      ANGLES ± 1°		CHECKED BY DFRISIELLO		02/08/2021				
THIRD-ANGLE PROJECTION 		APPROVED BY PHOSPODAR		02/08/2021		CATEGORY <div>FIBER OPTICS</div>		
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION SM ODVA to Duplex LC/UPC, OSP Jacket						
COLOR VARIATIONS MAY OCCUR		SIZE A		CAGE CODE 43321		ITEM NO. FOA1OOD8		REV. A
SCALE: NONE		CAD FILE: FOA1OOD8.SLDDRW					SHEET 1 OF 1	