



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	12/03/2019	GUTTADAURO
B	ECN 10616 EDIT TEXT	08/07/2020	GUTTADAURO



MODEL NUMBER	LENGTH FEET [METER]
TRG829-MMZ-1F	1 [.30]
TRG829-MMZ-3F	3 [.91]
TRG829-MMZ-5F	5 [1.52]
TRG829-MMZ-10F	10 [3.05]

NOTES:

1. TEST ASSEMBLY FOR SHORTS, CONTINUITY, AND INSULATION RESISTANCE 200 MEGAOHMS MIN.
2. TETHER FOR PROTECTIVE COVER INCLUDED BUT NOT SHOWN.
3. LABEL SHALL BE PLACED ON CABLE WITH P/N AND DATE CODE.
4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS		DATE		<div><div>L-com™</div><div>an INFINITI® brand</div></div> <div>50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936</div>	
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0		DRAWN BY BPUCHASKI		12/07/2006			
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] .XX = ± .02 [.5] .XXX = ± .005 [.13]		CHECKED BY DFRISIELLO		12/07/2006			
		APPROVED BY GUTTADAURO		12/03/2019			
		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY TELECOM/MODULAR			
THIRD-ANGLE PROJECTION 		COLOR VARIATIONS MAY OCCUR		PRODUCT DESCRIPTION C5e MM-M RJ45 801 AL/CD OLIVE LSZH W/ DC			
				SIZE A	CAGE CODE 43321	DWG. NO. TRG829-MMZ	REV. B
				SCALE: NONE CAD FILE: TRG829-MMZ.SLDDRW			SHEET 1 OF 1