




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	12/03/2019	GUTTADAURO
B	ECN 10616 EDIT TEXT	08/07/2020	GUTTADAURO



MODEL NUMBER	LENGTH FEET [METER]
TRG829-MFZ-1F	1 [.30]
TRG829-MFZ-10F	10 [3.05]

NOTES:

- TEST ASSEMBLY FOR SHORTS, CONTINUITY, AND INSULATION RESISTANCE 200 MEGAOHMS MIN.
- LABEL SHALL BE PLACED ON CABLE WITH P/N AND DATE CODE.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS		DATE		<div><div>an INFINITI<sup>®</sup> brand</div></div> <div>50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936</div>					
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0		DRAWN BY BPUCHASKI		12/03/2019							
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]      FRACTIONS .XX = ± .02 [.5]      ± 1/32 .XXX = ± .005 [.13]      ANGLES ± 1°		CHECKED BY DFRISIELLO		12/03/2019							
		APPROVED BY GUTTA DAURO		12/03/2019							
THIRD-ANGLE PROJECTION 		COLOR VARIATIONS MAY OCCUR		SIZE A		CAGE CODE 43321		DWG. NO. TRG829-MFZ		REV. B	
				SCALE: NONE		CAD FILE: TRG829-MFZ.SLDDRW				SHEET 1 OF 1	