


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	03/12/2021	GUTTADAURO



NOTES:

JACKET PROPERTIES:

JACKET IS SUNLIGHT RESISTANT, WELD SPLATTER RESISTANT,
AND CUTTING/MACHINING OIL RESISTANT.
TEMPERATURE RANGE: -40 ° C TO +75 ° C

FLEX LIFE:

1 MILLION CYCLE TEST (10X CABLE O.D. MINIMUM RADIUS)
10 MILLION CYCLE TEST (20X CABLE O.D. MINIMUM RADIUS)

AGENCY APPROVALS:

NEC (UL) TYPE CMX OUTDOOR - CM
CEC C(UL) TYPE CMX OUTDOOR - CM
UL AWM STYLE 2463

VOLTAGE RATING: 600 V MAX.


CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.



CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN
ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

MODEL NUMBER	LENGTH METERS [FEET]
TRG695RG1-05M	0.5 [1.64]
TRG695RG1-1M	1.0 [3.28]
TRG695RG1-2M	2.0 [6.56]
TRG695RG1-3M	3.0 [9.84]
TRG695RG1-5M	5.0 [16.41]
TRG695RG1-10M	10.0 [32.81]



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS		DATE		 an INFINIT® brand		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0		DRAWN BY DFRISIELLO		03/12/2021		CATEGORY TELECOM/MODULAR			
		CHECKED BY GUTTADAURO		03/12/2021					
		APPROVED BY GUTTADAURO		03/12/2021					
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS .XX = ± .02 [.5] ± 1/32 .XXX = ± .005 [.13] ANGLES ± 1°		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION IP68 RGRJ45 P/P ENICK TPE BLK					
THIRD-ANGLE PROJECTION 		COLOR VARIATIONS MAY OCCUR		SIZE A	CAGE CODE 43321	ITEM NO. TRG695RG1		REV. A	
				SCALE: NONE		CAD FILE: TRG695RG1.SLDDRW			SHEET 1 OF 1