


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	1/25/2022	JJOHNSTON





PART NUMBER	LENGTH METER [FEET]
FCA-SLCUSCUD2	2.0 [6.56]
FCA-SLCUSCUD5	5.0 [16.40]
FCA-SLCUSCUD10	10.0 [32.81]
FCA-SLCUSCUD15	15.0 [49.21]

#### NOTES:

- LC CONNECTOR 2 ASSEMBLY POLISH TYPE: UPC.
- SC CONNECTOR 2 ASSEMBLY POLISH TYPE: UPC.
- ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

#### REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS		DATE		 an INFINITI® brand		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936			
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0		DRAWN BY DMAY		1/18/22							
		CHECKED BY JJOHNSTON		1/25/22		CATEGORY					
		ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]   FRACTIONS ± 1/32 .XX = ± .02 [.5]   ANGLES ± 1° .XXX = ± .005 [.13]		APPROVED BY JJOHNSTON		1/25/22		FIBER OPTICS			
THIRD-ANGLE PROJECTION 		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION FIBER OPTIC PATCH CORD SM G652D DUPLEX LC/UPC-SC/UPC ARMORED 4.8mm LSZH BLACK							
				COLOR VARIATIONS MAY OCCUR		SIZE A	CAGE CODE 43321	ITEM NO. FCA-SLCUSCUD	REV. A		
				SCALE: NONE				CAD FILE: FCA-SLCUSCUD.SLDDRW		SHEET 1 OF 1	