


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	10/22/2021	PHOSPODAR

WIRING MAP TYPE B		
J1	COLOR	J2
1	BLUE	12
2	ORANGE	11
3	GREEN	10
4	BROWN	9
5		8
6		7
7		6
8		5
9	YELLOW	4
10	PURPLE	3
11	ROSE	2
12	AQUA	1



LENGTH	
ITEM NO.	METERS [FEET]
MPMF8SMBP-1	1.0 [3.28]
MPMF8SMBP-3	3.0 [9.84]
MPMF8SMBP-5	5.0 [16.40]
MPMF8SMBP-10	10.0 [32.81]

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS		DATE		 an INFINITI brand		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0		DRAWN BY DZINN		10/22/2021		CATEGORY		FIBER OPTICS	
		CHECKED BY DFRISIELLO		10/22/2021					
		APPROVED BY PHOSPODAR		10/22/2021					
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] .XX = ± .02 [.5] .XXX = ± .005 [.13]		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION Fiber patch cable MPO Male to MPO Female, 8 fiber SMF type B, OFNP rated					
THIRD-ANGLE PROJECTION 		COLOR VARIATIONS MAY OCCUR		SIZE A	CAGE CODE 43321	ITEM NO. MPMF8SMBP	REV. A		
				SCALE: NONE		CAD FILE: MPMF8SMBP.SLDDRW		SHEET 1 OF 1	