


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE  
PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE  
WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	10/21/2022	PHospodar



ITEM NUMBER	LENGTH METER [FEET]
FCA-S1SR-LCSC-01M	1.0 [3.28]
FCA-S1SR-LCSC-03M	3.0 [9.84]
FCA-S1SR-LCSC-05M	5.0 [16.40]
FCA-S1SR-LCSC-10M	10.0 [32.81]

NOTES:

- LC CONNECTOR ASSEMBLY POLISH TYPE: UPC.  
SC CONNECTOR ASSEMBLY POLISH TYPE: UPC.
- ALL CONNECTORS SUPPLIED WITH A DUST CAP INSTALLED, NOT SHOWN.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IAW L-COM  
SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS		DATE		<div>L-com<sup>™</sup> an INFINITI<sup>®</sup> brand</div>		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936			
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0		DRAWN BY DZINN		10/21/2022		CATEGORY		FIBER OPTIC			
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]   FRACTIONS XX = ± .02 [.5]   ± 1/32 .XXX = ± .005 [.13]   ANGLES ± 1°		CHECKED BY DFRISIELLO		10/21/2022		APPROVED BY JJohnston		PRODUCT DESCRIPTION FIBER PATCH CABLE ASSY, 9/125 SINGLE MODE, OS1, LSZH, LCU-SCU			
THIRD-ANGLE PROJECTION 		COLOR VARIATIONS MAY OCCUR		SIZE <b>A</b>		CAGE CODE <b>43321</b>		ITEM NO. FCA-S1SZ-LCSC		REV. <b>A</b>	
				SCALE: NONE		CAD FILE: FCA-S1SZ-LCSC.SLDDRW				SHEET 1 OF 1	