


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE
PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE
WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	03/19/2021	PHOSPODAR

		WIRING MAP			
D	J1	COLOR	J2	J3	J4
	1	BLUE	12		
	2	ORANGE	11		
	3	GREEN	10		
	4	BROWN	9		
	5	GRAY		12	
	6	WHITE		11	
	7	RED		10	
	8	BLACK		9	
	9	YELLOW			12
C	10	PURPLE			11
	11	ROSE			10
	12	AQUA			9
	13	BLUE w/TRACER	4		
	14	ORANGE w/TRACER	3		
	15	GREEN w/TRACER	2		
	16	BROWN w/TRACER	1		
	17	GRAY w/TRACER		4	
	18	WHITE w/TRACER		3	
	19	RED w/TRACER		2	
B	20	BLACK w/TRACER		1	
	21	YELLOW w/TRACER			4
	22	PURPLE w/TRACER			3
	23	ROSE w/TRACER			2
	24	AQUA w/TRACER			1



NOTES:

1. MPO CONNECTOR SINGLE MODE ASSEMBLY POLISH TYPE: APC
2. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
3. PACKAGING: INDIVIDUALLY PACKAGE EACH ASSEMBLY IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

PART NUMBER	METERS (FEET)
MPF24308SMZ-1	1.0 (3.28)
MPF24308SMZ-3	3.0 (9.84)
MPF24308SMZ-5	5.0 (16.40)
MPF24308SMZ-10	10.0 (32.81)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS		DATE		 an INFINITO™ brand		750 High Street, West Mill, North Andover, MA 01845 USA Phone: 1.800.341.5266 1.978.682.6936		
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0		DRAWN BY DZIN		03/19/2021		CATEGORY		FIBER OPTIC		
		CHECKED BY DFRISIELLO		03/19/2021						
		APPROVED BY PHOSPODAR		03/19/2021						
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] .XX = ± .02 [.5] .XXX = ± .005 [.13]		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION FIBER CONV HARNESS, MPO24 (F) TO 3XMPO8 (F)						
THIRD-ANGLE PROJECTION 		COLOR VARIATIONS MAY OCCUR		SIZE A		CAGE CODE 43321		ITEM NO. MPF24308SMZ		REV A
				SCALE: NONE		CAD FILE: MPF24308SMZ.SLDDRW			SHEET 1 OF	