


8 7 6 5 4 3 2 1

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	03/17/21	PHOSPODAR

WIRING MAP			
J1	COLOR	J2	J3
	BLUE		
2	ORANGE	12	
3	GREEN	11	
4	BROWN	10	
5	GRAY	9	
6	WHITE		12
7	RED		11
8	BLACK		10
9	YELLOW		9
	PURPLE		
	ROSE		
	AQUA		
	BLUE w/TRACER		
14	ORANGE w/TRACER	1	
15	GREEN w/TRACER	2	
16	BROWN w/TRACER	3	
17	GRAY w/TRACER	4	
18	WHITE w/TRACER		1
19	RED w/TRACER		2
20	BLACK w/TRACER		3
21	YELLOW w/TRACER		4
	PURPLE w/TRACER		
	ROSE w/TRACER		
	AQUA w/TRACER		



PART NUMBER	METERS (FEET)
MPF24212OM4Z-CA-1	1.0 (3.28)
MPF24212OM4Z-CA-3	3.0 (9.84)
MPF24212OM4Z-CA-5	5.0 (16.40)
MPF24212OM4Z-CA-10	10.0 (32.81)

- NOTES:
- MPO CONNECTOR MULTIMODE ASSEMBLY POLISH TYPE: UPC
 - ALL CONNECTORS INCLUDE A DUST CAP (NOT SHOWN).
 - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS		DATE		 an INFINITO brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0		DRAWN BY DZINN		03/17/21			
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS .XX = ± .02 [-.5] ± 1/32 .XXX = ± .005 [-.13] ANGLES ± 1°		CHECKED BY DFRISIELLO		03/17/21			
THIRD-ANGLE PROJECTION		APPROVED BY PHOSPODAR		03/17/21			
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY		FIBER OPTICS			
COLOR VARIATIONS MAY OCCUR		PRODUCT DESCRIPTION		FIBER AG CONV HARNESS, MPO24 (F) TO 2XMPO12 (F)			
SIZE A		CAGE CODE 43321		ITEM NO. MPF24212OM4Z-CA		REV. A	
SCALE: NONE		CAD FILE: MPF24212OM4Z-CA.SLDDRW				SHEET 1 OF 1	