


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE
PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE
WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	11/18/20	PHOSPODAR

		WIRING MAP			
D	PAIR	LC	1X24	REF	DES
	P1	1	1	P1	
		13	13		
	P2	2	2		
		14	14		
P3	3	3			
	15	15			
C	P4	4	4		
		16	16		
	P5	5	5		
		17	17		
	P6	6	6		
		18	18		
	P7	7	7		
		19	19		
	P8	8	8		
		20	20		
	P9	9	9		
		21	21		
B	10	10	10		
		22	22		
	P11	11	11		
		23	23		
	P12	12	12		
		24	24		



PART NUMBER	METERS (FEET)
MPM24OM4-20LCR-1	1.0 (3.28)
MPM24OM4-20LCR-3	3.0 (9.84)
MPM24OM4-20LCR-5	5.0 (16.40)
MPM24OM4-20LCR-10	10.0 (32.81)

NOTES:

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS		DATE		 an INFINITI brand 7500 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 > 12 [305] ≤ 60 [1524] = +2 [51] / -0 > 60 [1524] ≤ 120 [3048] = +4 [102] / -0 > 120 [3048] ≤ 300 [7620] = +6 [152] / -0 > 300 [7620] = +5% / -0		DRAWN BY DFRISIELLO		11/18/2020			
		CHECKED BY PHOSPODAR		11/18/2020			
		APPROVED BY PHOSPODAR		11/18/2020		CATEGORY FIBER OPTICS	
ALL OTHER DIMENSIONAL TOLERANCES: $.X = \pm .2$ [5] $.XX = \pm .02$ [.5] $.XXX = \pm .005$ [.13]		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION MPO w/ pins to LC fanout fiber, 2.0mm diameter, 24 fiber, OM4 50/125um			
THIRD-ANGLE PROJECTION 		COLOR VARIATIONS MAY OCCUR		SIZE A	CAGE CODE 43321	ITEM NO. MPM24OM4-20LCR	REV. A
				SCALE: NONE		CAD FILE: MPM24OM4-20LCR.SLDDRW	
						SHEET 1 OF 1	