



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE
PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE
WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	11/18/2020	PHOSPODAR



NOTES:

1. COMPONENT SHALL BE INDIVIDUALLY PACKAGED
IN ACCORDANCE WITH L-COM SPECIFICATION LSP-010-1.
2. ALL DIMENSIONS FOR REFERENCE ONLY.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS		DATE		<div><div><div>L-com[™]</div><div>an INFINITI[®] brand</div></div><div>50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936</div></div>	
OVERALL CABLE LENGTH TOLERANCE:		DRAWN BY DZINN		11/18/2020			
≤12 [305] = +1 [25] / -0		CHECKED BY DFRISIELLO		11/18/2020			
≤120 [3048] = +4 [102] / -0		APPROVED BY PHOSPODAR		11/18/2020			
≤300 [7620] = +6 [152] / -0						CATEGORY	
≤300 [7620] = +5% / -0						FIBER OPTIC	
ALL OTHER DIMENSIONAL TOLERANCES:		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION			
.X = ± .2 [5] FRACTIONS ± 1/32				FIBER OPTIC MATING SLEEVE CAP AND CHAIN, METAL, ST CONNECTOR STYLE			
.XX = ± .02 [.5] ANGLES ± 1°							
.XXX = ± .005 [.13]							
THIRD-ANGLE PROJECTION		COLOR VARIATIONS MAY OCCUR		SIZE A		CAGE CODE 43321	
				ITEM NO.		FOC-STMSC	
				SCALE: NONE		CAD FILE: FOC-STMSC.SLDDRW	
						REV. A	
						SHEET 1 OF 1	