


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	08/11/2021	PHOSPODAR





ITEM NO.	LENGTH	
	METER	FEET
FCA-LCLC-DPM3P-01	1.0	3.28
FCA-LCLC-DPM3P-02	2.0	6.56
FCA-LCLC-DPM3P-03	3.0	9.84
FCA-LCLC-DPM3P-05	5.0	16.40
FCA-LCLC-DPM3P-07	7.0	22.97
FCA-LCLC-DPM3P-10	10.0	32.81
FCA-LCLC-DPM3P-15	15.0	49.21

**NOTES:**

- LC CONNECTOR POLISH TYPE: UPC.
- ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**  
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]  OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0  ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5]      FRACTIONS ± 1/32 .XX = ±.02 [.5]    ANGLES ± 1° .XXX = ±.005 [.13]	APPROVALS	DATE	 an INFINITI brand  50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY DZINN	08/11/2021	
	CHECKED BY DFRISIELLO	08/11/2021	
	APPROVED BY PHOSPODAR	08/11/2021	
THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY <b>FIBER OPTICS</b>
	COLOR VARIATIONS MAY OCCUR		PRODUCT DESCRIPTION <b>FIBER OPTIC PATCH CABLE LC TO LC DUPLEX 50/125 MULTIMODE OM3 OFNP</b>
	SIZE <b>A</b>	CAGE CODE <b>43321</b>	ITEM NO. <b>FCA-LCLC-DPM3P</b>
SCALE: NONE		CAD FILE: FCA-LCLC-DPM3P.SLDDRW	REV. <b>A</b>