


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	2/4/22	JJOHNSTON



PART NUMBER	LENGTH METERS [FEET]
FCA-MMS206600P	0.5 [1.64]
FCA-MMS206601P	1.0 [3.28]


WIRING MAP	
MPO FIBER #	COLOR
1	N/A
2	N/A
3	N/A
4	BLUE
5	ORANGE
6	GREEN
7	BROWN
8	GREY
9	WHITE
10	N/A
11	N/A
12	N/A

#### NOTES:

1. LC CONNECTOR ASSEMBLY POLISH TYPE: PC
2. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

#### REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS		DATE		<div><div><div>L-com<sup>™</sup></div><div>an INFINITI<sup>®</sup> brand</div></div></div>		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0		DRAWN BY DMAY		1/26/22					
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]      FRACTIONS ± 1/32 .XX = ± .02 [.5]      ANGLES ± 1° .XXX = ± .005 [.13]		CHECKED BY DFRISIELLO		1/28/22		CATEGORY		FIBER OPTICS	
		APPROVED BY JJOHNSTON		2/4/22					
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION		PATCH CORD MM OM2 6CORES MPO(MALE, STANDARD LOSS)-LC/PC 0.25mm PVC 6COLOUR					
THIRD-ANGLE PROJECTION 		COLOR VARIATIONS MAY OCCUR		SIZE <b>A</b>	CAGE CODE <b>43321</b>	ITEM NO. <b>FCA-MMS20660</b>	REV. <b>A</b>		
				SCALE: NONE		CAD FILE: FCA-MMS20660.SLDDRW		SHEET 1 OF 1	