


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	01/25/2022	JJOHNSTON




PART NUMBER	LENGTH METER [FEET]
FCA-SFCASCAD2	2.0 [6.56]
FCA-SFCASCAD5	5.0 [16.40]
FCA-SFCASCAD10	10.0 [32.81]
FCA-SFCASCAD15	15.0 [49.21]

NOTES:

1. FC CONNECTOR 2 ASSEMBLY POLISH TYPE: APC.
2. SC CONNECTOR 2 ASSEMBLY POLISH TYPE: APC.
3. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS		DATE		<div>L-com[™] an INFINITE[®] brand</div>		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0		DRAWN BY DMAY		1/18/22		CATEGORY FIBER OPTICS			
		CHECKED BY JJOHNSTON		1/25/22					
		APPROVED BY JJOHNSTON		1/25/22					
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS .XX = ± .02 [.5] ± 1/32 .XXX = ± .005 [.13] ANGLES ± 1°		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION FIBER OPTIC PATCH CORD SM G652D DUPLEX FC/APC-SC/APC ARMORED 4.8mm LSZH, BLACK					
THIRD-ANGLE PROJECTION 		COLOR VARIATIONS MAY OCCUR		SIZE A	CAGE CODE 43321	ITEM NO. FCA-SFCASCAD		REV. A	
				SCALE: NONE		CAD FILE: FCA-SFCASCAD.SLDDRW		SHEET 1 OF 1	