



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	11/18/2019	GUTTADAURO



WIRING MAP	
1	WHITE
2	GREEN
3	YELLOW
4	GRAY
5	PINK
6	RED
7	BLACK
8	VIOLET
9	GRAY/PINK
10	RED/BLUE
11	WHITE/GREEN
12	BROWN/GREEN
13	WHITE/YELLOW
14	YELLOW/BROWN
15	WHITE/GRAY
16	GRAY/BROWN
-1	--
+1	BROWN
-2	BLUE
+2	--
PE	GREEN/YELLOW



SECTION A-A





CONNECTOR  
PIN OUT  
(ROTATED 90° CCW)

**SPECIFICATIONS:**

19 CONDUCTOR- STRANDED BARE COPPER  
SINGLE CORD FILLER, BLACK PVC JACKET  
WIRE INSULATION: PVC  
OUTER JACKET COLOR: GRAY  
OUTER JACKET MATERIAL: PUR  
OUTER JACKET DIAMETER: 10.0mm +/-5% NOM.  
BEND RADIUS: 10 X OUTER DIAMETER  
TEMPERATURE RANGE: -30° C TO +80° C  
CABLE APPROVAL: UL (AWM-STYLE 21441/10955), CE  
SHIELDING: NONE  
CHEMICAL RESISTANCE: GOOD RESISTANCE TO OIL,  
GASOLINE AND CHEMICALS (EN 60811-404)  
NOMINAL VOLTAGE: 300V AC  
TEST VOLTAGE: 2000V AC

HOUSING: PLASTIC, FLAME RETARDANT  
TOTAL CURRENT: 8A MAX.  
HOUSING SCREW: 2X, M3 PAN HEAD X 15.75mm LG

CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN  
ACCORDANCE WITH L-COM SPECIFICATION PS-0031

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5]   FRACTIONS ± 1/32 .XX = ±.02 [.5]   ANGLES ± 1° .XXX = ±.005 [.13]	APPROVALS	DATE	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY DFRISIELLO	11/14/2019	
	APPROVED BY GUTTADAURO	11/18/2019	CATEGORY TELECOM/MODULAR
THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	PRODUCT DESCRIPTION M12 TRM CABLE 5M
	SIZE <b>A</b>	CAGE CODE <b>43321</b>	DWG. NO. M12DBC8W-TRM-5M
	SCALE: NONE	CAD FILE: M12DBC8W-TRM-5M.LDDRW	REV. <b>A</b>