


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

8 7 6 5 4 3 2 1

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	1/25/2022	JJOHNSTON



PART NUMBER	LENGTH METER [FEET]
FCA-SMUUMUUS2	2.0 [6.56]
FCA-SMUUMUUS5	5.0 [16.40]
FCA-SMUUMUUS10	10.0 [32.81]
FCA-SMUUMUUS15	15.0 [49.21]

NOTES:

1. MU CONNECTOR ASSEMBLY POLISH TYPE: UPC.
2. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

**REGULATORY COMPLIANCE:**

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS	DATE	L-com an INFINITe brand	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0	DRAWN BY DMAY	1/20/22			
	CHECKED BY JJOHNSTON	1/25/22			
	APPROVED BY JJOHNSTON	1/25/22			
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			PRODUCT DESCRIPTION		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]      FRACTIONS .XX = ± .02 [5]      ± 1/32 .XXX = ± .005 [13]      ANGLES ± 1°			FIBER OPTIC PATCH CORD SM G652D SIMPLEX MU/UPC-MU/UPC ARMORED 2.0mm LSZH BLACK		
THIRD-ANGLE PROJECTION			SIZE <b>A</b>	CAGE CODE <b>43321</b>	
COLOR VARIATIONS MAY OCCUR			ITEM NO. <b>FCA-SMUUMUUS</b>	REV. <b>A</b>	
SCALE: NONE			CAD FILE: FCA-SMUUMUUS.SLDDRW	SHEET 1 OF 1	